

# WA86M5E20 Cut Sheet



Wiegmann enclosure, NEMA 12, 86 x 187 x 20in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 5-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA86M5E20>

## Technical Specifications

|                                 |                   |                                  |                                            |
|---------------------------------|-------------------|----------------------------------|--------------------------------------------|
| <b>Brand</b>                    | Wiegmann          | <b>Knockouts</b>                 | No                                         |
| <b>Item</b>                     | Enclosure         | <b>Material</b>                  | Carbon steel                               |
| <b>Subpanel</b>                 | Subpanel included | <b>Color</b>                     | ANSI 61 gray                               |
| <b>Slope Top</b>                | No                | <b>Finish</b>                    | Powder coat                                |
| <b>NEMA Rating</b>              | 12                | <b>Cover Type</b>                | 5-door                                     |
| <b>Nominal Enclosure Height</b> | 86in              | <b>Hinge Type</b>                | Continuous hinge                           |
| <b>Nominal Enclosure Width</b>  | 187in             | <b>Number of Hinges Per Door</b> | 1                                          |
| <b>Nominal Enclosure Depth</b>  | 20in              | <b>Latch Type</b>                | 3-point keylocking/padlocking combo handle |
| <b>Mounting</b>                 | Freestanding      | <b>Padlockable</b>               | Yes                                        |
| <b>Dual Access</b>              | No                | <b>Keylocking</b>                | Yes                                        |

## Agency Approvals

|                             |                                        |
|-----------------------------|----------------------------------------|
| <b>UL Listed File #</b>     | E64791                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |