

WA86M5E Cut Sheet



Wiegmann enclosure, NEMA 12, 86 x 187 x 14in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 5-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA86M5E>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Subpanel	Subpanel included
Slope Top	No
NEMA Rating	12
Nominal Enclosure Height	86in
Nominal Enclosure Width	187in
Nominal Enclosure Depth	14in
Mounting	Freestanding
Dual Access	No

Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	5-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point keylocking/padlocking combo handle
Padlockable	Yes
Keylocking	Yes

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document