

# WA90XM7724U Cut Sheet



Wiegmann disconnect enclosure, NEMA 12, right flange, 90 x 77 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point padlocking handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WA90XM7724U>

## Technical Specifications

|                          |                      |
|--------------------------|----------------------|
| Brand                    | Wiegmann             |
| Item                     | Disconnect enclosure |
| Slope Top                | No                   |
| NEMA Rating              | 12                   |
| Disconnect Mounting      | Right flange         |
| Nominal Enclosure Height | 90.13in              |
| Nominal Enclosure Width  | 78.5in               |
| Nominal Enclosure Depth  | 25.29in              |
| Mounting                 | Freestanding         |
| Material                 | Carbon steel         |
| Color                    | ANSI 61 gray         |
| Finish                   | Powder coat          |

|                           |                                                                                                                   |
|---------------------------|-------------------------------------------------------------------------------------------------------------------|
| Cover Type                | 2-door                                                                                                            |
| Hinge Type                | Continuous hinge                                                                                                  |
| Number of Hinges Per Door | 1                                                                                                                 |
| Latch Type                | 3-point padlocking handle                                                                                         |
| Padlockable               | Yes                                                                                                               |
| Keylocking                | No                                                                                                                |
| Subpanel                  | Subpanel included                                                                                                 |
| Requires                  | Operator adapter plate (sold separately)                                                                          |
| Additional Information    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                      |                                        |
|----------------------|----------------------------------------|
| UL Listed File #     | E64791                                 |
| UL Recognized File # | None                                   |
| UL Hazardous File #  | None                                   |
| CE                   | None                                   |
| CSA File #           | None                                   |
| RoHS Status          | No                                     |
| EU REACH             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/WA90XM7724U.pdf>  
See store item page for other formats.