

WC08C08 Cut Sheet



Wiegmann operator console, NEMA 12/13, 8 x 8 x 7in (HxWxD), desktop or pedestal mount, carbon steel, ANSI 61 gray, powder coat finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WC08C08>

Technical Specifications

Brand	Wiegmann
Item	Operator console
NEMA Rating	12/13
Nominal Enclosure Dimensions	8 x 8 x 7in (HxWxD)
Enclosure Height	8.31in
Enclosure Width	8.31in
Enclosure Depth	7.10in
Mounting	Desktop or pedestal
Integral Mounting Feet	No
Integral Mounting Flange	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Additional Information	Purchase pedestal column separately

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document