

WC08C12 Cut Sheet



Wiegmann operator console, NEMA 12/13, 8 x 12 x 7in (HxWxD), desktop or pedestal mount, carbon steel, ANSI 61 gray, powder coat finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WC08C12>

Technical Specifications

| | |
|-------------------------------------|----------------------|
| Brand | Wiegmann |
| Item | Operator console |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 12/13 |
| Nominal Enclosure Dimensions | 8 x 12 x 7in (HxWxD) |
| Enclosure Height | 8.31in |
| Enclosure Width | 12.31in |
| Enclosure Depth | 7.10in |
| Mounting | Desktop or pedestal |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |

| | |
|----------------------------------|-------------------------------------|
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Shelf | No |
| Padlockable | No |
| Keylocking | No |
| Additional Information | Purchase pedestal column separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WC08C12.pdf>
See store item page for other formats.