

# WC08C20 Cut Sheet



Wiegmann operator console, NEMA 12/13, 8 x 20 x 7in (HxWxD), desktop or pedestal mount, carbon steel, ANSI 61 gray, powder coat finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WC08C20>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Operator console
<b>NEMA Rating</b>	12/13
<b>Nominal Enclosure Height</b>	8in
<b>Nominal Enclosure Width</b>	20in
<b>Nominal Enclosure Depth</b>	7in
<b>Mounting</b>	Desktop or pedestal
<b>Integral Mounting Feet</b>	No

<b>Integral Mounting Flange</b>	No
<b>Material</b>	Carbon steel
<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Hinge Type</b>	Continuous hinge
<b>Number of Hinges Per Door</b>	1
<b>Additional Information</b>	Purchase pedestal column separately

## Agency Approvals

<b>UL Listed File #</b>	E64791
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/WC08C20.pdf>  
See store item page for other formats.