

WC1224B Cut Sheet



Wiegmann operator console, NEMA 12/13, 36 x 24 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, flush single-door, 3-point keylocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WC1224B>

Technical Specifications

Brand	Wiegmann
Item	Operator console
Subpanel	Subpanel included
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	12/13
Nominal Enclosure Dimensions	36 x 24 x 24in (HxWxD)
Enclosure Height	36.13in
Enclosure Width	24.13in
Enclosure Depth	24.06in
Mounting	Freestanding
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No

Knockouts	No
Bottom Gland Plate	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Flush single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point keylocking handle
Shelf	No
Padlockable	No
Keylocking	Yes
Additional Information	Purchase optional console top, writing desk and/or caster kit separately

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WC1224B.pdf>
See store item page for other formats.