

WC12B Cut Sheet



Wiegmann operator console, NEMA 12/13, 36 x 36 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, flush single-door, 3-point keylocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WC12B>

Technical Specifications

Brand	Wiegmann
Item	Operator console
Subpanel	Subpanel included
NEMA Rating	12/13
Nominal Enclosure Dimensions	36 x 36 x 24in (HxWxD)
Enclosure Height	36.13in
Enclosure Width	36.13in
Enclosure Depth	24.06in
Mounting	Freestanding
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Flush single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point keylocking handle
Padlockable	No
Keylocking	Yes
Additional Information	Purchase optional console top, writing desk and/or caster kit separately

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document