

WC12B Cut Sheet



Wiegmann operator console, NEMA 12/13, 36 x 36 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, flush single-door, 3-point keylocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WC12B>

Technical Specifications

Brand	Wiegmann	Knockouts	No
Item	Operator console	Bottom Gland Plate	No
Subpanel	Subpanel included	Material	Carbon steel
Slope Top	No	Color	ANSI 61 gray
3-Piece Assembly	No	Finish	Powder coat
Vented	No	Cover Type	Flush single-door
NEMA Rating	12/13	Hinge Type	Continuous hinge
Nominal Enclosure Dimensions	36 x 36 x 24in (HxWxD)	Number of Hinges Per Door	1
Enclosure Height	36.13in	Latch Type	3-point keylocking handle
Enclosure Width	36.13in	Shelf	No
Enclosure Depth	24.06in	Padlockable	No
Mounting	Freestanding	Keylocking	Yes
Integral Mounting Feet	No	Additional Information	Purchase optional console top, writing desk and/or caster kit separately
Integral Mounting Flange	No		
Dual Access	No		

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WC12B.pdf>
See store item page for other formats.