

WC12C24SS Cut Sheet



Wiegmann operator console, NEMA 4/4X/12/13, 12 x 24 x 9in (HxWxD), desktop or pedestal mount, 304 stainless steel, No. 3 intermediate polished finish.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WC12C24SS>

Technical Specifications

| | |
|-------------------------------------|-----------------------|
| Brand | Wiegmann |
| Item | Operator console |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 4/4X/12/13 |
| Nominal Enclosure Dimensions | 12 x 24 x 9in (HxWxD) |
| Enclosure Height | 12.31in |
| Enclosure Width | 24.31in |
| Enclosure Depth | 9.10in |
| Mounting | Desktop or pedestal |
| Integral Mounting Feet | No |

| | |
|----------------------------------|----------------------------------|
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | 304 stainless steel |
| Finish | No. 3 intermediate polished |
| Hinge Type | Stainless steel continuous hinge |
| Number of Hinges Per Door | 1 |
| Shelf | No |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WC12C24SS.pdf>
See store item page for other formats.