

WC1448BD Cut Sheet



Wiegmann operator console, NEMA 12/13, 50 x 48 x 23in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, flush double-door, 3-point keylocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WC1448BD>

Technical Specifications

Brand	Wiegmann
Item	Operator console
Subpanel	Purchase subpanel separately
NEMA Rating	12/13
Nominal Enclosure Height	50in
Nominal Enclosure Width	48in
Nominal Enclosure Depth	23in
Mounting	Freestanding
Material	Carbon steel
Color	ANSI 61 gray

Finish	Powder coat
Cover Type	Flush double-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point keylocking handle
Padlockable	No
Keylocking	Yes
Additional Information	Purchase optional console top, writing desk and/or caster kit separately

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WC1448BD.pdf>
See store item page for other formats.