

WC936B Cut Sheet



Wiegmann operator console, NEMA 12/13, 48 x 36 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point keylocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WC936B>

Technical Specifications

Brand	Wiegmann	Dual Access	No
Item	Operator console	Knockouts	No
Subpanel	Purchase subpanel(s) separately	Bottom Gland Plate	No
Slope Top	No	Material	Carbon steel
3-Piece Assembly	No	Color	ANSI 61 gray
Vented	No	Finish	Powder coat
NEMA Rating	12/13	Cover Type	Single-door
Nominal Enclosure Dimensions	48 x 36 x 18in (HxWxD)	Hinge Type	Continuous hinge
Enclosure Height	48.13in	Number of Hinges Per Door	1
Enclosure Width	36.00in	Latch Type	3-point keylocking handle
Enclosure Depth	19.03in	Shelf	No
Mounting	Freestanding	Padlockable	No
Integral Mounting Feet	No	Keylocking	Yes
Integral Mounting Flange	No	Additional Information	Purchase optional caster kit separately

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WC936B.pdf>
See store item page for other formats.