

WG-175-020-H Cut Sheet



IronHorse heavy-duty worm gearbox, 20:1 ratio, 56C-Face input, hollow, 1in diameter output shaft, nominal 0.75hp at 1.0 SF, 737 lb-in mechanical output torque, 1-3/4in center distance, cast iron housing, tapped-base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WG-175-020-H>

Technical Specifications

Brand	IronHorse
Item	Gearbox
Application	General purpose
Duty Rating	Heavy-duty
Gearbox Type	Worm
Gear Ratio	20:1
Speed Rating	1750rpm input / 88rpm output
Input Configuration	56C-Face
Input Power Rating	Nominal 0.75hp at 1.0 SF
Output Configuration	Hollow

Gearbox Output Shaft Diameter	1in
Mechanical Output Torque	596 lb-in
Thermal Output Torque	572 lb-in
Center Distance	1-3/4in
Housing Material	Cast iron
Mounting	Tapped-base
Finish	Anti-corrosion primer and paint
Lubrication Type	Pre-filled with synthetic lube
Oil Seal Type	Double-lip

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WG-175-020-H.pdf>
See store item page for other formats.