


WG-175-020-L Cut Sheet



IronHorse heavy-duty worm gearbox, 20:1 ratio, 56C-Face input, left hand, 0.875in diameter output shaft, nominal 0.75hp at 1.0 SF, 737 lb-in mechanical output torque, 1-3/4in center distance, cast iron housing, tapped-base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WG-175-020-L>

Technical Specifications

| | |
|--------------------------------------|---------------------------------|
| Brand | IronHorse |
| Item | Gearbox |
| Application | General purpose |
| Duty Rating | Heavy-duty |
| Gearbox Type | Worm |
| Gear Ratio | 20:1 |
| Speed Rating | 1750rpm input / 88rpm output |
| Input Configuration | 56C-Face |
| Input Power Rating | Nominal 0.75hp at 1.0 SF |
| Output Configuration | Left hand |
| Gearbox Output Shaft Diameter | 0.875in |
| Mechanical Output Torque | 596 lb-in |
| Thermal Output Torque | 572 lb-in |
| Center Distance | 1-3/4in |
| Housing Material | Cast iron |
| Mounting | Tapped-base |
| Finish | Anti-corrosion primer and paint |
| Lubrication Type | Pre-filled with synthetic lube |
| Oil Seal Type | Double-lip |

Agency Approvals

| | |
|--------------------|--|
| RoHS Status | No |
| EU REACH | View EU REACH document |