


WG-175-060-L Cut Sheet



IronHorse heavy-duty worm gearbox, 60:1 ratio, 56C-Face input, left hand, 0.875in diameter output shaft, nominal 0.25hp at 1.0 SF, 433 lb-in mechanical output torque, 1-3/4in center distance, cast iron housing, tapped-base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WG-175-060-L>

Technical Specifications

Brand	IronHorse
Item	Gearbox
Application	General purpose
Duty Rating	Heavy-duty
Gearbox Type	Worm
Gear Ratio	60:1
Speed Rating	1750rpm input / 29rpm output
Input Configuration	56C-Face
Input Power Rating	Nominal 0.25hp at 1.0 SF
Output Configuration	Left hand
Gearbox Output Shaft Diameter	0.875in
Mechanical Output Torque	469 lb-in
Thermal Output Torque	469 lb-in
Center Distance	1-3/4in
Housing Material	Cast iron
Mounting	Tapped-base
Finish	Anti-corrosion primer and paint
Lubrication Type	Pre-filled with synthetic lube
Oil Seal Type	Double-lip

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document