

# WG-206-040-H Cut Sheet



IronHorse heavy-duty worm gearbox, 40:1 ratio, 56C-Face input, hollow, 1.125in diameter output shaft, nominal 0.5hp at 1.0 SF, 1120 lb-in mechanical output torque, 2-1/16in center distance, cast iron housing, tapped-base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WG-206-040-H>

## Technical Specifications

<b>Brand</b>	IronHorse
<b>Item</b>	Gearbox
<b>Application</b>	General purpose
<b>Duty Rating</b>	Heavy-duty
<b>Gearbox Type</b>	Worm
<b>Gear Ratio</b>	40:1
<b>Speed Rating</b>	1750rpm input / 44rpm output
<b>Input Configuration</b>	56C-Face
<b>Input Power Rating</b>	Nominal 0.5hp at 1.0 SF
<b>Output Configuration</b>	Hollow

<b>Gearbox Output Shaft Diameter</b>	1.125in
<b>Mechanical Output Torque</b>	1120 lb-in
<b>Thermal Output Torque</b>	726 lb-in
<b>Center Distance</b>	2-1/16in
<b>Housing Material</b>	Cast iron
<b>Mounting</b>	Tapped-base
<b>Finish</b>	Anti-corrosion primer and paint
<b>Lubrication Type</b>	Pre-filled with synthetic lube
<b>Oil Seal Type</b>	Double-lip

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/WG-206-040-H.pdf>  
See store item page for other formats.