


# WG-262-060-R Cut Sheet



IronHorse heavy-duty worm gearbox, 60:1 ratio, 56C-Face input, right hand, 1.125in diameter output shaft, nominal 0.75hp at 1.0 SF, 1670 lb-in mechanical output torque, 2-5/8in center distance, cast iron housing, tapped-base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WG-262-060-R>

## Technical Specifications

<b>Brand</b>	IronHorse	<b>Gearbox Output Shaft Diameter</b>	1.125in
<b>Item</b>	Gearbox	<b>Mechanical Output Torque</b>	1670 lb-in
<b>Application</b>	General purpose	<b>Thermal Output Torque</b>	1346 lb-in
<b>Duty Rating</b>	Heavy-duty	<b>Center Distance</b>	2-5/8in
<b>Gearbox Type</b>	Worm	<b>Housing Material</b>	Cast iron
<b>Gear Ratio</b>	60:1	<b>Mounting</b>	Tapped-base
<b>Speed Rating</b>	1750rpm input / 29rpm output	<b>Finish</b>	Anti-corrosion primer and paint
<b>Input Configuration</b>	56C-Face	<b>Lubrication Type</b>	Pre-filled with synthetic lube
<b>Input Power Rating</b>	Nominal 0.75hp at 1.0 SF	<b>Oil Seal Type</b>	Double-lip
<b>Output Configuration</b>	Right hand		

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>