


WG-325-060-DA Cut Sheet



IronHorse heavy-duty worm gearbox, 60:1 ratio, 56C-Face input, dual, 1.375in diameter output shaft, nominal 2hp at 1.0 SF, 3127 lb-in mechanical output torque, 3-1/4in center distance, cast iron housing, tapped-base mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WG-325-060-DA>

Technical Specifications

| | |
|-----------------------------|------------------------------|
| Brand | IronHorse |
| Item | Gearbox |
| Application | General purpose |
| Duty Rating | Heavy-duty |
| Gearbox Type | Worm |
| Gear Ratio | 60:1 |
| Speed Rating | 1750rpm input / 29rpm output |
| Input Configuration | 56C-Face |
| Input Power Rating | Nominal 2hp at 1.0 SF |
| Output Configuration | Dual |

| | |
|--------------------------------------|---------------------------------|
| Gearbox Output Shaft Diameter | 1.375in |
| Mechanical Output Torque | 3127 lb-in |
| Thermal Output Torque | 2476 lb-in |
| Center Distance | 3-1/4in |
| Housing Material | Cast iron |
| Mounting | Tapped-base |
| Finish | Anti-corrosion primer and paint |
| Lubrication Type | Pre-filled with synthetic lube |
| Oil Seal Type | Double-lip |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | none |
| UL Recognized File # | none |
| UL Hazardous File # | none |
| CE | None |
| CSA File # | none |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WG-325-060-DA.pdf>
See store item page for other formats.