

WGA-40M-010-63B14 Cut Sheet



IronHorse medium-duty worm gearbox, 10:1 ratio, IEC 63B14 input, hollow, 18mm diameter output shaft, nominal 1.21hp at 1.0 SF, 370 lb-in mechanical output torque, 40mm center distance, cast aluminum housing, top, bottom and back mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WGA-40M-010-63B14>

Technical Specifications

Brand	IronHorse	Mechanical Output Torque	370 lb-in
Item	Gearbox	Thermal Output Torque	370 lb-in
Application	General purpose	Center Distance	40mm
Duty Rating	Medium-duty	Housing Material	Cast aluminum
Gearbox Type	Worm	Mounting	Top, bottom and back
Gear Ratio	10:1	Finish	Powder coat
Speed Rating	1750rpm input / 175rpm output	Lubrication Type	Pre-filled with synthetic lube
Input Configuration	IEC 63B14	Oil Seal Type	Double-lip
Input Power Rating	Nominal 1.21hp at 1.0 SF	Includes	Motor mounting hardware
Output Configuration	Hollow		
Gearbox Output Shaft Diameter	18mm		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/WGA-40M-010-63B14.pdf>
See store item page for other formats.