


# WGA-63M-100-H1 Cut Sheet



IronHorse medium-duty worm gearbox, 100:1 ratio, 56C-Face input, hollow, 1.125in diameter output shaft, nominal 0.5hp at 1.0 SF, 1035 lb-in mechanical output torque, 63mm center distance, cast aluminum housing, top and bottom mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WGA-63M-100-H1>

## Technical Specifications

<b>Brand</b>	IronHorse
<b>Item</b>	Gearbox
<b>Application</b>	General purpose
<b>Duty Rating</b>	Medium-duty
<b>Gearbox Type</b>	Worm
<b>Gear Ratio</b>	100:1
<b>Speed Rating</b>	1750rpm input / 18rpm output
<b>Input Configuration</b>	56C-Face
<b>Input Power Rating</b>	Nominal 0.5hp at 1.0 SF
<b>Output Configuration</b>	Hollow
<b>Gearbox Output Shaft Diameter</b>	1.125in
<b>Mechanical Output Torque</b>	1035 lb-in
<b>Thermal Output Torque</b>	1035 lb-in
<b>Center Distance</b>	63mm
<b>Housing Material</b>	Cast aluminum
<b>Mounting</b>	Top and bottom
<b>Includes</b>	Motor mounting hardware
<b>Finish</b>	Anti-corrosion epoxy paint
<b>Lubrication Type</b>	Pre-filled with synthetic lube
<b>Oil Seal Type</b>	Double-lip

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>