

WKK-AP-4H Cut Sheet



AutomationDirect inductive proximity sensor, tubular, 18mm diameter x 65mm body, weld coated brass housing, PNP, N.O. output, 12mm sensing distance, non-flush, 2 kHz switching frequency, IP67, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WKK-AP-4H>

Technical Specifications

Brand	AutomationDirect
Item	Proximity sensor
Sensor Type	Inductive
Application	Welding and factor 1
Shape	Tubular
Housing Size	18mm diameter x 65mm body
Housing Material	Weld coated brass
Barrel Type	Threaded
Sensing Method	Extended sensing, factor 1
Adjustable	No
Number of Wires	3
Switching Output	PNP
Operation Mode	N.O. output

Sensing Distance	12mm
Mounting Type	Non-flush
IO-Link Compatible	No
Switching Frequency	2 kHz
Operating Voltage	10-30 VDC
Operating Temperature	-25 to 70c
Weld Field Immune	Yes
Chip Immune	No
IP Rating	IP67
Connection	4-pin M12 quick-disconnect
Includes	Mounting hardware
Additional Information	Purchase cable separately

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WKK-AP-4H.pdf>
See store item page for other formats.