

WKM-AP-3H Cut Sheet



AutomationDirect inductive proximity sensor, tubular, 12mm diameter x 65mm body, weld coated brass housing, PNP, N.O. output, 4mm sensing distance, flush, 2 kHz switching frequency, IP65 IP66 IP67 IP68 IP69K, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WKM-AP-3H>

Technical Specifications

| | |
|-------------------------|----------------------------|
| Brand | AutomationDirect |
| Item | Proximity sensor |
| Sensor Type | Inductive |
| Application | Welding and factor 1 |
| Shape | Tubular |
| Housing Size | 12mm diameter x 65mm body |
| Housing Material | Weld coated brass |
| Barrel Type | Threaded |
| Sensing Method | Extended sensing, factor 1 |
| Adjustable | No |
| Number of Wires | 3 |
| Switching Output | PNP |
| Operation Mode | N.O. output |

| | |
|-------------------------------|----------------------------|
| Sensing Distance | 4mm |
| Mounting Type | Flush |
| IO-Link Compatible | No |
| Switching Frequency | 2 kHz |
| Operating Voltage | 10-30 VDC |
| Operating Temperature | -40 to 85C |
| Weld Field Immune | Yes |
| Chip Immune | No |
| IP Rating | IP65 IP66 IP67 IP68 IP69K |
| Connection | 4-pin M12 quick-disconnect |
| Includes | Mounting hardware |
| Additional Information | Purchase cable separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E328811 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |