

WLL25 Cut Sheet



Wall Lenk soldering iron, 25W, 900 deg F, 6ft cord. Pointed tip and tool stand included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WLL25>

Technical Specifications

Brand	Wall Lenk
Item	Soldering iron
Cordless	No
Wattage	25W
Maximum Tip Temperature	900 deg F
Soldering Tip Style	Pointed
Tip Length	.96in
Tip Diameter	.185in
Handle Length	4.75in
Handle Diameter	1in
Handle Material	Polycarbonate
Shaft Material	Stainless steel
Heat Up Time	5 minutes
Cord Length	6ft
Includes	Pointed tip and tool stand

Agency Approvals

UL Listed File #	E22261
RoHS Status	No
EU REACH	View EU REACH document