

# WLL40K Cut Sheet



Wall Lenk soldering iron, 40W, 975 deg F, 8ft cord. Pointed tip, chisel tip, fine pointed tip, 1/2 ounce lead free solder and tool stand included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WLL40K>

## Technical Specifications

<b>Brand</b>	Wall Lenk
<b>Item</b>	Soldering iron
<b>Cordless</b>	No
<b>Wattage</b>	40W
<b>Maximum Tip Temperature</b>	975 deg F
<b>Soldering Tip Style</b>	Pointed, chisel and fine point
<b>Tip Length</b>	1in
<b>Tip Diameter</b>	.25in
<b>Handle Length</b>	4.75in
<b>Handle Diameter</b>	1in
<b>Handle Material</b>	Polycarbonate
<b>Shaft Material</b>	Stainless steel
<b>Heat Up Time</b>	5 minutes
<b>Cord Length</b>	8ft
<b>Includes</b>	Pointed tip, chisel tip, fine pointed tip, 1/2 ounce lead free solder and tool stand

## Agency Approvals

<b>UL Listed File #</b>	E22261
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>