

WLL80T Cut Sheet



Wall Lenk screwdriver soldering tip, replacement, 995 deg F. For use with Wall Lenk soldering iron WLL80.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WLL80T>

Technical Specifications

Brand	Wall Lenk
Item	Soldering tip
Replacement	Yes
Soldering Tip Style	Screwdriver
Tip Length	1.75in
Tip Diameter	.375in
Wattage	80W
Maximum Tip Temperature	995 deg F
For Use With	Wall Lenk soldering iron WLL80

Agency Approvals

RoHS Status	No
EU REACH	View EU REACH document