

WLLG2500K Cut Sheet



Wall Lenk soldering gun, 100W, 850 deg F, 6ft cord. (2) conical tips and 6 grams of lead free rosin core solder included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WLLG2500K>

Technical Specifications

Brand	Wall Lenk
Item	Soldering gun
Cordless	No
Wattage	100W
Maximum Tip Temperature	850 deg F
Soldering Tip Style	Conical
Heat Up Time	1 minute
LED Work Light	Yes
Cord Length	6ft
Includes	(2) conical tips and 6 grams of lead free rosin core solder

Agency Approvals

UL Listed File #	E69348
RoHS Status	No
EU REACH	View EU REACH document