

# WLQ30SI Cut Sheet



Wall Lenk cordless soldering iron, 30W, 1100 deg F. Pointed tip, tool cap, safety stand and usb charging cable included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WLQ30SI>

## Technical Specifications

<b>Brand</b>	Wall Lenk
<b>Item</b>	Soldering iron
<b>Cordless</b>	Yes
<b>Wattage</b>	30W
<b>Maximum Tip Temperature</b>	1100 deg F
<b>Soldering Tip Style</b>	Pointed
<b>Tip Length</b>	1.56in
<b>Tip Diameter</b>	0.177in
<b>Charge Time</b>	3.5 hours
<b>Continuous Working Time</b>	40 minutes
<b>Handle Length</b>	7.5in

<b>Handle Diameter</b>	1in
<b>Handle Material</b>	Polycarbonate
<b>Heat Up Time</b>	12 seconds
<b>LED Work Light</b>	Yes
<b>Includes</b>	Pointed tip, tool cap, safety stand and usb charging cable
<b>Dangerous Goods</b>	<ul style="list-style-type: none"><li>• Hazard Type: Lithium Battery</li><li>• Packing Instruction: 966</li><li>• UN Number: UN3481</li><li>• Battery Included: True</li><li>• Battery Installed: Yes</li><li>• Battery Type: Other</li></ul>

## Agency Approvals

<b>UL Listed File #</b>	E22261
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>