

WLWG991KCS Cut Sheet



Wall Lenk soldering gun, 150W and 100W, 800 deg F, 8ft cord. Conical tip, bevel smoothing tip, knife cutting tip and 1/2 ounce lead free solder included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WLWG991KCS>

Technical Specifications

Brand	Wall Lenk
Item	Soldering gun
Cordless	No
Wattage	150W and 100W
Maximum Tip Temperature	800 deg F
Soldering Tip Style	Conical, bevel and knife
Heat Up Time	1 minute
LED Work Light	Yes
Cord Length	8ft
Includes	Conical tip, bevel smoothing tip, knife cutting tip and 1/2 ounce lead free solder

Agency Approvals

UL Listed File #	E22261
RoHS Status	No
EU REACH	View EU REACH document