

WMZT2D40 Cut Sheet



Eaton miniature circuit breaker, current-limiting, 40A, 240 VAC/48 VDC, 2-pole, D curve, thermal magnetic, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WMZT2D40>

Technical Specifications

Brand	Eaton
Item	Circuit breaker
Series	WMZ
Circuit Breaker Type	Miniature
Circuit Type	Feeder and branch
Current-Limiting	Yes
Amperage Rating	40A
Voltage Rating	240 VAC/48 VDC
Number of Poles	2

Trip Curve	D curve
Trip Type	Thermal magnetic
UL Rating	UL 489 listed
NEC Class 2	No
Mounting	35mm DIN rail
HACR Rated	Yes
Reverse Feed Capable	Yes
Manufacturer Part Number	WMZT2D40

Agency Approvals

UL Listed File #	E7819
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	245545
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WMZT2D40.pdf>
See store item page for other formats.