

# WMZT3D04 Cut Sheet



Eaton miniature circuit breaker, current-limiting, 4A, 480Y/277 VAC/96 VDC, 3-pole, D curve, thermal magnetic, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WMZT3D04>

## Technical Specifications

Brand	Eaton
Item	Circuit breaker
Series	WMZ
Circuit Breaker Type	Miniature
Circuit Type	Feeder and branch
Current-Limiting	Yes
Amperage Rating	4A
Voltage Rating	480Y/277 VAC/96 VDC

Number of Poles	3
Trip Curve	D curve
Trip Type	Thermal magnetic
UL Rating	UL 489 listed
Mounting	35mm DIN rail
HACR Rated	Yes
Reverse Feed Capable	Yes
Manufacturer Part Number	WMZT3D04

## Agency Approvals

UL Listed File #	E7819
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	245545
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/WMZT3D04.pdf>  
See store item page for other formats.