

WMZT3DX0 Cut Sheet



Eaton miniature circuit breaker, current-limiting, 0.5A, 480Y/277 VAC/96 VDC, 3-pole, D curve, thermal magnetic, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WMZT3DX0>

Technical Specifications

Brand	Eaton	Number of Poles	3
Item	Circuit breaker	Trip Curve	D curve
Series	WMZ	Trip Type	Thermal magnetic
Circuit Breaker Type	Miniature	UL Rating	UL 489 listed
Circuit Type	Feeder and branch	Mounting	35mm DIN rail
Current-Limiting	Yes	HACR Rated	Yes
Amperage Rating	0.5A	Reverse Feed Capable	Yes
Voltage Rating	480Y/277 VAC/96 VDC	Manufacturer Part Number	WMZT3DX0

Agency Approvals

UL Listed File #	E7819
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	245545
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WMZT3DX0.pdf>
See store item page for other formats.