

WPP-A-H-0250-N Cut Sheet

Gefran magnetostrictive linear position sensor, rodless slide, 250mm stroke, 0-10 and 10-0 VDC output, 28.3 x 32 x 404mm, channel mount, 8-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WPP-A-H-0250-N>

Technical Specifications

| | |
|-------------------------------|--|
| Brand | Gefran |
| Item | Linear position sensor |
| Transducer Type | Magnetostrictive |
| Action | Rodless slide |
| Stroke | 250mm |
| Output | 0-10 and 10-0 VDC |
| Housing Material | Anodized aluminum |
| Housing Size | 28.3 x 32 x 404mm |
| Operating Voltage | 19.2-28.8 VDC |
| Sensor Resolution | Infinite |
| Linearity | +/- 0.02% |
| Mounting | Channel |
| IP Rating | IP67 |
| Connection | 8-pin M12 quick-disconnect |
| Number of Wires | 8 |
| Additional Information | Purchase cursor and mounting brackets separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |