

WRD604818SSFSDN4 Cut Sheet



Wiegmann KwikHinge series enclosure, NEMA 3R/4/4X/12, 60 x 48 x 18in (HxWxD), freestanding mount, 304 stainless steel, No. 3 intermediate polished finish, 2-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WRD604818SSFSDN4>

Technical Specifications

Brand	Wiegmann
Item	Enclosure
Series	KwikHinge
Subpanel	Purchase subpanel separately
Slope Top	No
NEMA Rating	3R/4/4X/12
IP Rating	IP66
Nominal Enclosure Height	60in
Nominal Enclosure Width	48in
Nominal Enclosure Depth	18in
Mounting	Freestanding
Integral Mounting Feet	No

Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	304 stainless steel
Finish	No. 3 intermediate polished
Cover Type	2-door
Hinge Type	KwikHinge sliding hinge pins
Number of Hinges Per Door	3
Latch Type	3-point keylocking/padlocking combo handle
Number Of Latches	2
Padlockable	Yes
Keylocking	Yes

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WRD604818SSFSDN4.pdf>
See store item page for other formats.