

WRD72XM2718FS4 Cut Sheet



Wiegmann KwikHinge series disconnect enclosure, NEMA 3R/4/12, right flange, 72 x 27 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point keylocking/padlocking combo handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WRD72XM2718FS4>

Technical Specifications

| | |
|---------------------------------|----------------------|
| Brand | Wiegmann |
| Item | Disconnect enclosure |
| Series | KwikHinge |
| Slope Top | No |
| NEMA Rating | 3R/4/12 |
| IP Rating | IP66 |
| Disconnect Mounting | Right flange |
| Nominal Enclosure Height | 72.13in |
| Nominal Enclosure Width | 27.5in |
| Nominal Enclosure Depth | 19.29in |
| Mounting | Freestanding |
| Material | Carbon steel |

| | |
|----------------------------------|---|
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Single-door |
| Hinge Type | KwikHinge sliding hinge pins |
| Number of Hinges Per Door | 4 |
| Latch Type | 3-point keylocking/padlocking combo handle |
| Padlockable | Yes |
| Keylocking | Yes |
| Subpanel | Subpanel included |
| Additional Information | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E64791 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WRD72XM2718FS4.pdf>
See store item page for other formats.