

WRD72XM3918FS4 Cut Sheet



Wiegmann KwikHinge series disconnect enclosure, NEMA 3R/4/12, right flange, 72 x 39 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point keylocking/padlocking combo handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WRD72XM3918FS4>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Series	KwikHinge
Slope Top	No
Vented	No
NEMA Rating	3R/4/12
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	72 x 39 x 18in (HxWxD)
Enclosure Height	72.13in
Enclosure Width	39.50in
Enclosure Depth	19.29in

Mounting	Freestanding
Integral Mounting Feet	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	KwikHinge sliding hinge pins
Number of Hinges Per Door	4
Latch Type	3-point keylocking/padlocking combo handle
Padlockable	Yes
Keylocking	Yes
Subpanel	Purchase subpanel separately

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WRD72XM3918FS4.pdf>
See store item page for other formats.