

WRD72XM5318FSD4 Cut Sheet



Wiegmann KwikHinge series disconnect enclosure, NEMA 3R/4/12, right flange, 72 x 53 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point keylocking/padlocking combo handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WRD72XM5318FSD4>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Series	KwikHinge
Slope Top	No
NEMA Rating	3R/4/12
IP Rating	IP66
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	72 x 53 x 18in (HxWxD)
Enclosure Height	72.13in
Enclosure Width	53.50in
Enclosure Depth	19.29in
Mounting	Freestanding
Integral Mounting Feet	No
Integral Mounting Flange	No
Dual Access	No

Knockouts	No
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	2-door
Hinge Type	KwikHinge sliding hinge pins
Number of Hinges Per Door	4
Latch Type	3-point keylocking/padlocking combo handle
Padlockable	Yes
Keylocking	Yes
Subpanel	Subpanel included
Additional Information	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/WRD72XM5318FSD4.pdf>
See store item page for other formats.