

# WRD84XM7718FSD4 Cut Sheet



Wiegmann KwikHinge series disconnect enclosure, NEMA 3R/4/12, right flange, 84 x 77 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point keylocking/padlocking combo handle, subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WRD84XM7718FSD4>

## Technical Specifications

<b>Brand</b>	Wiegmann
<b>Item</b>	Disconnect enclosure
<b>Series</b>	KwikHinge
<b>Slope Top</b>	No
<b>NEMA Rating</b>	3R/4/12
<b>IP Rating</b>	IP66
<b>Disconnect Mounting</b>	Right flange
<b>Nominal Enclosure Height</b>	84.13in
<b>Nominal Enclosure Width</b>	78.5in
<b>Nominal Enclosure Depth</b>	19.29in
<b>Mounting</b>	Freestanding
<b>Material</b>	Carbon steel

<b>Color</b>	ANSI 61 gray
<b>Finish</b>	Powder coat
<b>Cover Type</b>	2-door
<b>Hinge Type</b>	KwikHinge sliding hinge pins
<b>Number of Hinges Per Door</b>	5
<b>Latch Type</b>	3-point keylocking/padlocking combo handle
<b>Padlockable</b>	Yes
<b>Keylocking</b>	Yes
<b>Subpanel</b>	Subpanel included
<b>Additional Information</b>	Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier

## Agency Approvals

<b>UL Listed File #</b>	E64791
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/WRD84XM7718FSD4.pdf>  
See store item page for other formats.