


WSE-A0-3A Cut Sheet



AutomationDirect inductive proximity sensor, tubular, 8mm diameter x 45mm body, weld coated 316 stainless steel housing, NPN/PNP, N.O. output, 2mm sensing distance, flush, 150 Hz switching frequency, IP67, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WSE-A0-3A>

Technical Specifications

Brand	AutomationDirect
Item	Proximity sensor
Sensor Type	Inductive
Application	Welding
Shape	Tubular
Housing Size	8mm diameter x 45mm body
Housing Material	Weld coated 316 stainless steel
Barrel Type	Threaded
Sensing Method	Extended sensing
Adjustable	No
Number of Wires	2
Switching Output	NPN/PNP
Operation Mode	N.O. output
Sensing Distance	2mm

Mounting Type	Flush
IO-Link Compatible	No
Switching Frequency	150 Hz
Operating Voltage	10-36 VDC
Operating Temperature	-25 to 70c
Weld Field Immune	No
Chip Immune	No
IP Rating	IP67
Connection	Pigtail
Conductor Size	22 AWG
Cable Length	9.8ft/3m
Jacket Material	PUR
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E328811
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document