

WT26028 Cut Sheet

Wiha 2.5mm slotted precision screwdriver, 5.9in (150mm) shaft length, cushion grip handle with rotating cap.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT26028>



Technical Specifications

Brand	Wiha	Shaft Length	5.9in (150mm)
Item	Screwdriver	Shaft Diameter	0.10in (2.5mm)
Screwdriver Type	Precision	Reduced Shank	No
Tip Type	Slotted	Finish	Chrome plated satin
Tip Size	2.5mm	Handle Length	3.7in (94mm)
Slotted Tip Thickness	0.4mm	Handle Type	Cushion grip handle with rotating cap
Insulated	No	Application	Screwdriving
Overall Length	9.6in (243mm)	Tool Features	Free-spinning cap

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document