

WT26042 Cut Sheet

Wiha 4mm slotted precision screwdriver, 5.9in (150mm) shaft length, cushion grip handle with rotating cap.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT26042>

Technical Specifications

Brand	Wiha
Item	Screwdriver
Screwdriver Type	Precision
Tip Type	Slotted
Tip Size	4mm
Insulated	No
Overall Length	10.2in (259mm)
Shaft Length	5.9in (150mm)
Shaft Diameter	0.16in (4.0mm)
Reduced Shank	No
Handle Length	4.3in (109mm)
Handle Type	Cushion grip handle with rotating cap
Application	Screwdriving

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document