

# WT26307 Cut Sheet



Wiha 0.7mm (.028in) external hex precision screwdriver, 1.6in (40mm) shaft length, cushion grip handle with rotating cap.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT26307>

---

## Technical Specifications

<b>Brand</b>	Wiha
<b>Item</b>	Screwdriver
<b>Screwdriver Type</b>	Precision
<b>Tip Type</b>	External hex
<b>Tip Size</b>	0.7mm (.028in)
<b>Insulated</b>	No
<b>Overall Length</b>	4.7in (119mm)
<b>Shaft Length</b>	1.6in (40mm)
<b>Shaft Diameter</b>	0.10in (2.5mm)
<b>Reduced Shank</b>	No
<b>Handle Length</b>	3.1in (79mm)
<b>Handle Type</b>	Cushion grip handle with rotating cap
<b>Application</b>	Screwdriving

---

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>