

# WT28188 Cut Sheet



Wiha Drive-Loc VI multi-bit adjustable shaft screwdriver, 32 pieces, imperial and metric, SoftFinish cushion grip blade lock handle, adjustable shaft length, slotted, Phillips, tamperproof torx, square, external hex and internal hex.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT28188>

## Technical Specifications

<b>Brand</b>	Wiha
<b>Series</b>	Drive-Loc VI
<b>Item</b>	Screwdriver
<b>Screwdriver Type</b>	Multi-bit adjustable shaft
<b>Number of Pieces</b>	32
<b>Ratcheting</b>	No
<b>Insulated</b>	No
<b>Measurement Type</b>	Imperial and metric
<b>Shaft Length</b>	Adjustable
<b>Shaft Diameter</b>	0.26in (6.5mm)
<b>Handle Length</b>	4.4in (112mm)
<b>Handle Type</b>	SoftFinish cushion grip blade lock handle
<b>Tip Type</b>	Slotted, Phillips, tamperproof torx, square, external hex and internal hex

<b>Includes</b>	(1) SoftFinish Drive-Loc VI handle, (17) Drive-Loc VI adjustable/reversible blades (Phillips (#0, #1, #2), slotted (3.0mm, 3.5mm, 4.0mm, 4.5mm, 5.5mm, 6.0mm, 6.5mm), square (#1, #2), Tamperproof Torx T6, T7, T8, T9, T10, T15, T20, T25, T30, T40), hex (3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 2.0mm, 2.5mm, 3.0mm, 4.0mm, 5.0mm, 6.0mm), (14) Drive-Loc VI adjustable nut drivers (1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 7/16in, 1/2in, 5.5mm, 6.0mm, 7.0mm, 8.0mm, 9.0mm, 10.0mm, 11.0mm), 38 Position Wiha Red and Black Wallet
<b>Application</b>	Screwdriving and nut driving
<b>Tool Features</b>	Adjustable shaft length from 1.7in to 4.8in in 1/8in increments

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>