

WT28188 Cut Sheet



Wiha Drive-Loc VI multi-bit adjustable shaft screwdriver, 32 pieces, imperial and metric, SoftFinish cushion grip blade lock handle, adjustable shaft length, slotted, Phillips, tamperproof torx, square, external hex and internal hex.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT28188>

Technical Specifications

Brand	Wiha
Series	Drive-Loc VI
Item	Screwdriver
Screwdriver Type	Multi-bit adjustable shaft
Number of Pieces	32
Ratcheting	No
Insulated	No
Measurement Type	Imperial and metric
Shaft Length	Adjustable
Shaft Diameter	0.26in (6.5mm)
Handle Length	4.4in (112mm)
Handle Type	SoftFinish cushion grip blade lock handle

Tip Type	Slotted, Phillips, tamperproof torx, square, external hex and internal hex
Includes	(1) SoftFinish Drive-Loc VI handle, (17) Drive-Loc VI adjustable/reversible blades (Phillips (#0, #1, #2), slotted (3.0mm, 3.5mm, 4.0mm, 4.5mm, 5.5mm, 6.0mm, 6.5mm), square (#1, #2), Tamperproof Torx T6, T7, T8, T9, T10, T15, T20, T25, T30, T40), hex (3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in, 2.0mm, 2.5mm, 3.0mm, 4.0mm, 5.0mm, 6.0mm), (14) Drive-Loc VI adjustable nut drivers (1/4in, 9/32in, 5/16in, 11/32in, 3/8in, 7/16in, 1/2in, 5.5mm, 6.0mm, 7.0mm, 8.0mm, 9.0mm, 10.0mm, 11.0mm), 38 Position Wiha Red and Black Wallet
Application	Screwdriving and nut driving

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document