

# WT28189 Cut Sheet



Wiha Drive-Loc VI multi-bit adjustable shaft screwdriver, 15 pieces, imperial and metric, SoftFinish cushion grip blade lock handle, adjustable shaft length, slotted, Phillips, tamperproof torx, external hex and square.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT28189>

## Technical Specifications

<b>Brand</b>	Wiha
<b>Series</b>	Drive-Loc VI
<b>Item</b>	Screwdriver
<b>Screwdriver Type</b>	Multi-bit adjustable shaft
<b>Number of Pieces</b>	15
<b>Ratcheting</b>	No
<b>Insulated</b>	No
<b>Measurement Type</b>	Imperial and metric
<b>Shaft Length</b>	Adjustable
<b>Shaft Diameter</b>	0.26in (6.5mm)
<b>Handle Length</b>	4.4in (112mm)

<b>Handle Type</b>	SoftFinish cushion grip blade lock handle
<b>Tip Type</b>	Slotted, Phillips, tamperproof torx, external hex and square
<b>Includes</b>	(1) SoftFinish Drive-Loc VI handle, (14) Drive-Loc VI adjustable/reversible blades (slotted (3.5mm, 4.5mm, 5.5mm, 6.5mm), Phillips (#1, #2), tamperproof torx (T6, T7, T8, T9, T10, T15, T20, T25, T30, T40), hex (2.0mm, 2.5mm, 3.0mm, 4.0mm, 5.0mm, 6.0mm, 3/32in, 7/64in, 1/8in, 9/64in, 5/32in, 3/16in), (1) cushion grip blade lock handle in canvas pouch
<b>Application</b>	Screwdriving

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>