

WT28198 Cut Sheet



Wiha Drive-Loc VI multi-bit adjustable shaft nutdriver, 8 pieces, metric, SoftFinish cushion grip blade lock handle, adjustable shaft length, internal hex.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT28198>

Technical Specifications

Brand	Wiha
Series	Drive-Loc VI
Item	Nutdriver
Screwdriver Type	Multi-bit adjustable shaft
Number of Pieces	8
Ratcheting	No
Insulated	No
Measurement Type	Metric
Shaft Length	Adjustable

Shaft Diameter	0.26in (6.5mm)
Handle Length	4.4in (112mm)
Handle Type	SoftFinish cushion grip blade lock handle
Tip Type	Internal hex
Includes	(1) SoftFinish Drive-Loc VI handle, (7) Drive-Loc VI adjustable nut setters (5.0mm, 5.5mm, 6.0mm, 7.0mm, 8.0mm, 9.0mm, 10.0mm), (1) cushion grip blade lock handle in canvas pouch
Application	Nut driving

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document