

# WT28310 Cut Sheet



Wiha SlimLine 3.5mm slotted insulated blade, 1000V insulation rating, 3.0in (76mm) shaft length, reduced shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT28310>

## Technical Specifications

<b>Brand</b>	Wiha	<b>Overall Length</b>	3.0in (76mm)
<b>Series</b>	SlimLine	<b>Shaft Length</b>	3.0in (76mm)
<b>Item</b>	Blade	<b>Shaft Diameter</b>	0.16in (4.0mm)
<b>Screwdriver Type</b>	Insulated	<b>Reduced Shank</b>	Yes
<b>Tip Type</b>	Slotted	<b>Finish</b>	Black oxide
<b>Tip Size</b>	3.5mm	<b>For Use With</b>	SlimLine series handles
<b>Slotted Tip Thickness</b>	0.6mm	<b>Application</b>	Screwdriving
<b>Insulated</b>	Yes	<b>Applicable Standards</b>	ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201
<b>Insulation Rating</b>	1000V		

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	None
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>