

WT28315 Cut Sheet



Wiha SlimLine 6.5mm slotted insulated blade, 1000V insulation rating, 3.0in (76mm) shaft length, reduced shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT28315>

Technical Specifications

Brand	Wiha	Overall Length	3.0in (76mm)
Series	SlimLine	Shaft Length	3.0in (76mm)
Item	Blade	Shaft Diameter	0.24in (6.1mm)
Screwdriver Type	Insulated	Reduced Shank	Yes
Tip Type	Slotted	Finish	Black oxide
Tip Size	6.5mm	For Use With	SlimLine series handles
Slotted Tip Thickness	1.2mm	Application	Screwdriving
Insulated	Yes	Applicable Standards	ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201
Insulation Rating	1000V		

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document