

WT28315 Cut Sheet



Wiha SlimLine 6.5mm slotted insulated blade, 1000V insulation rating, 3.0in (76mm) shaft length, reduced shank.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT28315>

Technical Specifications

Brand	Wiha
Series	SlimLine
Item	Blade
Screwdriver Type	Insulated
Tip Type	Slotted
Tip Size	6.5mm
Insulated	Yes
Insulation Rating	1000V

Overall Length	3.0in (76mm)
Shaft Length	3.0in (76mm)
Shaft Diameter	0.24in (6.1mm)
Reduced Shank	Yes
Application	Screwdriving
Applicable Standards	ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document