

WT28345 Cut Sheet



Wiha SlimLine PocketMax insulated multi-bit screwdriver, 1000V insulation rating, 6 pieces, SoftFinish cushion grip handle with bit storage, 2.0in (50mm) shaft length, slotted, Phillips and square.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT28345>

Technical Specifications

| | | | |
|-------------------|---------------------|----------------------|--|
| Brand | Wiha | Handle Length | 4.3in (109mm) |
| Series | SlimLine PocketMax | Handle Type | SoftFinish cushion grip handle with bit storage |
| Item | Screwdriver | Tip Type | Slotted, Phillips and square |
| Screwdriver Type | Insulated multi-bit | Includes | (1) insulated Pocketmax handle with bit storage, (5) insulated SlimLine bits (slotted: 3.5mm, 6.5mm, Phillips: (#1, #2), square: (#2)) |
| Number of Pieces | 6 | Application | Screwdriving |
| Ratcheting | No | Applicable Standards | ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201 |
| Insulated | Yes | | |
| Insulation Rating | 1000V | | |
| Overall Length | 6.8in (173mm) | | |
| Shaft Length | 2.0in (50mm) | | |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | No |
| EU REACH | View EU REACH document |