

WT28345 Cut Sheet



Wiha SlimLine PocketMax insulated multi-bit screwdriver, 1000V insulation rating, 6 pieces, Softfinish cushion grip handle with bit storage, 2.0in (50mm) shaft length, slotted, Phillips and square.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WT28345>

Technical Specifications

Brand	Wiha
Series	SlimLine PocketMax
Item	Screwdriver
Screwdriver Type	Insulated multi-bit
Number of Pieces	6
Insulation Rating	1000V
Overall Length	6.8in (173mm)
Handle Type	Softfinish cushion grip handle with bit storage
Handle Length	4.3in (109mm)
Shaft Length	2.0in (50mm)
Tip Type	Slotted, Phillips and square
Application	Screwdriving
Applicable Standards	ASTM F-1505-0, CSA, EN/IEC 60900 and VDE 0682/part 201
Includes	(1) insulated Pocketmax handle with bit storage, (5) insulated SlimLine bits (slotted: 3.5mm, 6.5mm, Phillips: (#1, #2), square: (#2))

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document